

Arktis Laser Product Datasheet

LQS-1053 Passively Q-Switched Laser System



Series Specifications:

| Nominal Wavelength | 1053 nm |
|--------------------|------------|
| Output Type | Q-Switched |
| Laser Source Type | DPSS |

Overview:

The LQS-1053 Series of Diode-Pumped Solid-State (DPSS) Q-Switched Lasers are ideal for applications requiring a very high peak power or short pulse duration at 1053 nm.

These lasers are commonly used for Raman spectroscopy, material processing, and a broad range of other applications. The driver is available as a plugand-play benchtop system or an O.E.M. component designed for system integration.

Key Features:

- Pulse energy of 10 uJ 50 uJ
- Pulse repetition rate of 1 Hz 5 kHz
- Pulse duration in the range of 6-10 ns
- Air cooled
- Runs on standard AC power (85 264 V, 47 63 Hz)
- 10,000 hour maintenance-free operating life (Expected)
- FDA/CDRH compliant Class IV enclosure

Package Includes:

- Laser Head
- Driver/Power Supply
- Power Cable
- BNC Connector (LabSpec models only)
- Keys, Safety Interlock
- Hard-shell Carrying Case

Specifications:

This spec sheet has been generated specifically for part number QA5-M, per your request, and data for the entire series is also displayed for your reference. The specs which are specific to QA5-M have been highlighted below in **red + bold**.

| O-11 D (140) | F0 400 | 450 050 |
|---|-------------------------------|---------------------------|
| Output Power (mW) | >50, >100 | >150, >250 |
| Single Pulse Energy (µJ) | 10, 20 | 30, 50 |
| Optimal Pulse Frequency (Hz) | 5000 | 5000 |
| Output Power Stability (%RMS/4h) | <1, <3, <5, <10 | <1, <3, <5, <10 |
| Central Wavelength (nm) | 1053.3 | 1053.3 |
| Wavelength Tolerance (+/- nm) | 1 | 1 |
| Divergence (mrad, full angle) | <1.5 | <2 |
| Beam Dimensions (mm, 1/e²) | 1.5 | 3 |
| Warm-up Time (minutes) | 10 | 10 |
| Avg. Pulse Duration (ns) | 10 | 10 |
| Approximate Peak Power (W) | 1500 | 3000, 10000 |
| Optical Noise Amplitude (%RMS @ 20 Hz - 20 MHz) | <20 | <20 |
| M² | <1.2 | <1.5 |
| Beam Pointing Stability (mrad) | <0.05 | <0.05 |
| Operating Temperature Range (°C) | 10 to 35 | 10 to 35 |
| Max. TTL Modulation Freq. (Hz) | 20000 | 20000 |
| Minimum Pulsing Frequency (Hz) | 1 | 1 |
| Modulation Input Signal | 0-5 VDC | 0-5 VDC |
| Total Power Consumption (W) | 25 | 80 |
| Max. Power Input Duty Cycle | 100% | 100% |
| Standard Warranty (months) | 12 | 12 |
| MTTF (operational hours) | 10000 | 10000 |
| Weight of Product or Laser Head (kg) | 0.6 | 0.9 |
| Beam Height from Base Plate (mm) | 24.8 | 29 |
| Dimensions of Product or Laser Head (mm) | 140.8 (I) x 73 (w) x 46.2 (h) | 155 (l) x 77 (w) x 60 (h) |

CW: All specifications are based on performance at full output power and after the specified warmup period. Output characteristics may change if the

laser is run at a different power level.

Q-Switched: Specifications are based on the laser pulsing at the specified design frequency. Output characteristics may change if the laser is run at a different frequency.

Specifications Page 2:

| l acar | Form | Factor | |
|--------|------|--------|--|

CW: All specifications are based on performance at full output power and after the specified warmup period. Output characteristics may change if the laser is run at a different power level.

Q-Switched: Specifications are based on the laser pulsing at the specified design frequency. Output characteristics may change if the laser is run at a different frequency.

Power Supply Options:

These lasers are available with several different power supply options. The model that you have selected is highlighted below, and any other options are shown for easy reference.

| | Power Supply Type: | OM |
|--------|-----------------------------|---------------------------|
| OEM AC | Input Power | 85v to 264v |
| | Power Supply Weight (kg) | 0.2 |
| | Dimensions (mm) | 100 (l) x 60 (w) x 56 (h) |

| | Power Supply Type: | FM | FH |
|-----------------------|-----------------------------|-------------------------------|--------------------------------|
| FDA-Compliant LabSpec | Input Power | 85v to 264v | 85v to 264v |
| | Power Supply Weight (kg) | 1.5 | 2.6 |
| | Dimensions (mm) | 154 (l) x 155 (w) x 95 (h) | 268 (I) x 145 (w) x 106 (h) |

| | Power Supply Type: | SM | SH |
|------------------------|-----------------------------|-------------------------------|--------------------------------|
| FDA-Compliant Standard | Input Power | 85v to 264v | 85v to 264v |
| 重 | Power Supply Weight (kg) | 1.2 | 2.3 |
| | Dimensions (mm) | 133 (l) x 130 (w) x 65 (h) | 238 (I) x 146 (w) x 102 (h) |

^{*}Power supply may not be exactly as shown, see dimensional drawings on next 2 pages.


Regulatory Classification:

The model you have selected (QA5-M) requires the following safety label(s):



^{*}Dimensions for fiber-integrated (I_) include laser head packaged inside.

Dimensional Drawing - Laser Form Factor: M:



Accessories:

The most popular accessories for model QA5-M are shown below. For additional details regarding these or other accessories please see our website or contact us directly.

| Part Number | Description | |
|-------------|--|---------------------|
| AGFA647XX | LSG-1064-NF-7 Fit-Over Safety Goggles 1064nm Output: OD 7+ at 950-1070 nm CE Certified Full Details: www.arktislaser.com/AGF | |
| ACFMIRHXA | FC/PC Fiber Coupler/Collimator for IR wavelengths (1000 to 1300 nm) (installed and aligned) 11mm diameter input lens Full Details: www.arktislaser.com/ACF | |
| ACSMIRHXA | SMA-905 Fiber Coupler/Collimator for IR wavelengths (1000 to 1300 nm) (installed and aligned) 11mm diameter input lens Full Details: www.arktislaser.com/ACS | |
| AFF2002XX | Armored Fiber With FC/PC Connectors 200um Core Multimode 2m length Full Details: www.arktislaser.com/AFF | |
| AFS2002XX | Armored Fiber With SMA 905 Connectors 200um Core Multimode 2 m length Full Details: www.arktislaser.com/AFS | |
| ACALBMXXX | Carrying Case-102 Holds Lab/OEM M, R and S size, standard or LabSpec laser Full Details: www.arktislaser.com/ACA | Included With Laser |

FOR MORE INFORMATION PLEASE CONTACT:

Arktis Laser
112 Elizabeth St, Unit 5-331, Toronto, ON, Canada M5G 1P5
Tel. 1-416-886-1178 Fax 1-647-874-7129
sales@arktislaser.com www.arktislaser.com

E&OE: Data included in this sheet may be subject to change without notice.

Please confirm critical specifications with our staff prior to ordering.